

Agilent InfinityLab LC Solutions

Join Us - Become a Part of the InfinityLab Success Story



Agilent A-Line Quick Connect Fittings



Save time, reduce cost, and minimize troubleshooting with A-Line Quick Connect fittings

With a Quick Connect fitting, you can be sure you're getting a perfect column connection, every time.

- Truly finger-tight connection: No special training is needed, so differences in user style will not affect your chromatography
- Spring-loaded design pushes the tubing against the receiving port for zero-dead-volume connections
- Compatibility with all types of columns by simply adjusting the ferrule • Reusable for more than 200 reconnections: Quick Connect fittings are long lasting, reseal tightly, and are stable up to 1,300 bar (18,850 psi)
- Fast, easy connections that save you time and trouble—particularly during method development and column testing